

KLOSZE

Covers

PL
Wymiary [mm]:
1000, 2020, 3000

EN
Dimensions [mm]:
1000, 2020, 3000

	TRANSPARENTNY PVC/PC transparent PVC/PC	MROŻONY PVC/PC frozen PVC/PC	MLECZNY PVC/PC milky PVC/PC	TRANSPARENTNY PMMA transparent PMMA	MROŻONY PMMA frozen PMMA	MLECZNY PMMA milky PMMA / 00000000 PMMA	FROSTED MLECZNY PMMA milky frosted PMMA PMMA	Prismatic PC	Czarny PMMA black PMMA	SREBRNY silver
BASIC										
HIGH* tylko PC i PMMA / only PC and PMMA										
WIDE										
SLIM										
DOUBLE										
TERRA										
SLIM LENS 15										
BASIC LENS 15										
BASIC LENS 30										
SUPERWIDE										
PLEXI TIANO PLEXI SUPERWIDE										
RASTER WIDE										

PRZEPUSZCZALNOŚĆ / TRANSPARENCY*

RODZAJE KŁOSZY type of covers	TEMPERATURA PRACY MATERIAŁU operating temperature of material	BASIC V2	HIGH	WIDE	SLIM	DOUBLE	TERRA	SLIM LENS 15	BASIC LENS 15	BASIC LENS 30	SUPERWIDE	PLEXI TIANO PLEXI SUPERWIDE	
DO PROFILI MEBLOWYCH fits furniture profiles		A / B / C / D / G / H / W / Y / Z	A / D		X / MICO			X / MICO	A / B / C / D / G / H / W / Y / Z				
DO PROFILI ARCHITEKTONICZNYCH fits architectural profiles		COSMO / RETO / TIANO / FLARO / MONO		SOLIS / INSO / ILEDO	SILEDA / INSILEDA / DILEDA / INDILEDA / UNICO / DOPIOTALIA / INTALIA / ZATI / SUBLI / LOGI / CONVA / TOPO / PERO / VEDA		TERRA / SCALA / RUNO		COSMO / RETO / MONO			LARGO / INLARGO / SORGA	TIANO LARGO / INLARGO SORGA
TRANSPARENTNY PVC transparent PVC		88%		85%	84%								
MROŻONY PVC frozen PVC	-20°C +65°C	66%		55%	63%								
MLECZNY PVC milky PVC		48%		28%	38%							40%	
TRANSPARENTNY PMMA transparent PMMA		95%	95%	94%	95%	93%		96%		92%	93%		
MROŻONY PMMA frozen PMMA	-20°C +70°C	78%	78%	73%	79%	79%							
MLECZNY PMMA milky PMMA		48%	52%	42%	39%	50%						72%	
FROSTED MLECZNY PMMA milky frosted PMMA		83%	83%	74%	83%	75%						76%	
TRANSPARENTNY PC transparent PC				91%									
MROŻONY PC frozen PC	-50°C +100°C			63%									
MLECZNY PC milky PC				30%			56%						
PRISMATIC PC				87%									
CZARNY PMMA black PMMA	-20°C +70°C	24%	20%		23%	23%							

* Wszystkie badania zostały wykonane w laboratorium fotometrii Lumines. Tolerancja wyniku $\pm 5\%$
 * All tests were carried out in the Lumines photometry laboratory. Result tolerance $\pm 5\%$.